

Aspire Evoke 2 Wheelchair



- The Evoke 2 is designed for the user who wants a lightweight, highly adjustable manual wheelchair
- **APPROVED for vehicle transport with user seated and headrest attached. Headrest (WCA848480) must be bought separately - please see the **Optional Accessories** below.**
- The [Contoured Padded Overlay](#) (shown in image #2) is a stylish recommended accessory for the Aspire Evoke 2. The contoured padded overlay offers the user increased comfort and is ideal for those who are in their wheelchair for longer periods of time. The mild contouring assists in positioning and pressure distribution, while the fabric allows air movement, increasing breathability. It is easily removed to allow washing when required
- Swing-in / out, height adjustable and removable foot rests – this facilitates user transfers and allows optimal positioning for the changing needs of the user
- Strong, Nylon upholstery with a comfortable cushion and padded backrest. For increased comfort, a padded overlay is available as an accessory
- Depth adjustable seating with rear angle adjustability – for more accurate positioning, customisability and increased user comfort
- Quick release 24" solid rear tyres - the wheels are easily removed to reduce the weight of the chair for transport and storage.
- Crash Tested – to AS/NZ3616.196

✓ Contracted DVA product

✓ Contract approved

Support @ Home

Function: Manual wheelchairs

Category: Prescribed

Click [here](#) for more information

NDIS

Item Code:

05_122203104_0105_1_2

Wheelchair Manual –

Composite:05_417_0105_1_2

Click [here](#) for more information

Compliance

AS3696-1:2008

Prescribing Therapists: Click here to download our
[Clinical Assistance Guide](#)

Warranty Information

- 2 Years Frame
- 1 Year Components

Code	Display Name	Safe Working Load	Material	Unit Weight	Colour	Seat Depth	Seat Width	Seat To Floor Height	Seat To Footrest	Backrest Height
MWS449500	Aspire Evoke 2 - 350mm Wide	150 kg	Aluminium	14.8 kg	Silver	300 - 450 mm	350 mm	440 - 480 mm	440 - 480 mm	430 - 490 mm
MWS449510	Aspire Evoke 2 - 400mm Wide	150 kg	Aluminium	14.9 kg	Silver	300 - 450 mm	400 mm	440 - 480 mm	440 - 480 mm	430 - 490 mm
MWS449520	Aspire Evoke 2 - 450mm Wide	150 kg	Aluminium	15.0 kg	Silver	300 - 450 mm	450 mm	440 - 480 mm	440 - 480 mm	430 - 490 mm
MWS449530	Aspire Evoke 2 - 500mm Wide	150 kg	Aluminium	15.1 kg	Silver	400 - 550 mm	500 mm	440 - 480 mm	440 - 480 mm	430 - 490 mm
WCA848592	Attendant Brakes Kit without Wheels	-	-	-	-	-	-	-	-	-
WCA848594	Attendant Propelled Conversion Kit with Brakes and Wheels	120 kg	-	-	-	-	-	-	-	-